



LOOK TO PSI
Optical Laboratory
Supplies & Equipment

Finishing & Dispensing Equipment



Heavy Duty Hand Edger Part #: HEM300

- Heavy duty 1/4 HP motor for use in a high production lab
- Durable housing with wide front hand rest to reduce operator fatigue
- Adjustable coolant spout with easy shut off
- Comes with 6", 600 grit v-bevel wheel (other wheel types and grits available, contact PSI for more information)
- 1700 rpm spindle speed, 115V, 6A
- Recommend using PSI's 952 Recycling & Filtration System for circulating the water. If a water tank is already in place, we recommend a water pump, PSI part#2467, to circulate the water.



Hand Edger Part #s: 1245CHBV (beveled wheel); 1245CH (flat wheel)

- Ergonomically designed for use on all lens materials
- Corrosion proof with drainage at the bottom
- Provides continuous flow of fresh water which eliminates contamination problems
- Includes lightweight, dual 300/600 grit, 4" retrieveable wheel (available with or without bevel)
- 100-120V, 60Hz



Mini Hand Edger For Pin Beveling Part #: NH-100

- For pin beveling only with angled bevel wheel for precise beveling
- Space saving, ergonomic and economical
- Low maintenance, no belts and mess free, no drain hose required
- 100-120V, 60Hz



Auto Groover Part #: NH-800

- Easy to learn, easy to use groover for plastic and polycarbonate
- Strong motor with durable rocker switches
- Variable groove position with center, front and rear leans reference points
- Depth and location of groove is easily adjusted
- Includes an all purpose wheel and half-eye chucks
- 100-120V, 60Hz Groove Depth: 0.07mm Lens Diameter: 17-70mm Lens Thickness: 2-11mm



Klear-Edge Polisher Part #: 2500-P

- Inexpensive way to produce lustrous lens edges on CR-39 and polycarbonate lens edges
- Easy to use and production proven since 1982
- Polisher comes with 1-felt polishing pad and 1-multi-purpose polish bar
- Replacement Supplies: 2503 - Multi-purpose polish bar; 2502 - Replacement felt polishing pad

Plug In Foot Pedal



Easy to use foot pedal for hand edgers. Just plug hand edger into the adapter on the electrical cord. Non-skid cover and base provides stable actuation.
PSI Part #: FP-10

To Order Call 800-237-8154 or Fax 800-330-3800



PRACTICAL SYSTEMS INC.
11617 Prospect Drive • Odessa, FL 33556
(800) 237-8154 • Fax (800) 330-3800
www.LookToPSI.com



Finishing & Dispensing Equipment



Polariscopes Part #: NH-15

- Identifies stress on mounted lenses, verifies that glass lenses are tempered/hardened properly and confirms polarization of lenses.
- Simple, easy to use, economical piece of equipment



Progressive Lens Identifier Part #: NH-29B

- Easily identify laser engravings by placing a lens under the LED light and looking at it in the magnifier
- Makes it easy to see the laser etchings to help eliminate errors in fitting progressive lenses



Photochromic Lens Activator Part #: NH-329

- Quick and easy way to activate photochromic lenses for analysis or demonstration
- Perfect for dispensary demonstrations without going outside
- UV lamp range is 365-405nm



Ultrasonic Cleaner Part #: CD-4800

- Designed for high volume use in busy offices and wholesale labs with a large, 45 oz. tank to hold multiple pairs of glasses
- Advanced digital control system offers five cycle times (90, 180, 280, 380 and 480 seconds) for enhanced efficiency. Push button controls and large digital time readout make it easy to operate
- A strong transducer provides 42,000Hz of wave frequency at 60 watts of power for great cleaning results



Futura Ultrasonic Cleaner Part #: CD-2800

- Sleek contemporary design looks great in dispensing area
- Quiet operation with automatic shut off after approximately 3 minute cycle time
- Blue indicator light on lid shows when in operation
- 20 oz. (600ml) stainless steel tank. Includes protective basket

Hot Air Frame Warmer Part #: NH-320

- Variable temperature adjustment helps prevent frame damage
- Compact and quiet running
- Offers instant heat and cold air with no warming up



Pupilometer Part #: HX-400

- Compact and lightweight with easy to read digital display
- View both monocular and binocular readings simultaneously
- Take distance PD and pupilometer will calculate near, measures PD's from 45-82mm
- Automatically shuts off after not being used for one minute. Uses 2 AA batteries

To Order Call 800-237-8154 or Fax 800-330-3800

