




LOOK TO PSI
Optical Laboratory
Supplies & Equipment

THE TRANSFORMER



The Transformer all-materials fining pad transforms as it fines from its original course state to a smoother, transparent condition. The innovative composition of this one-step and two-step pad allows it to breakdown during processing by fining the lens at different intensities, starting rough for heavy stock removal and easing down to transparent for an ultra smooth lens finish. This very unique pad achieves consistent stock-removal on all lens materials.



Features & Benefits:

- Unique pad composition allows it to transform as it fines from course to a smooth leaving a superb surface finish on all lens
- Consistent high stock removal rates for polycarbonate, trivex and all plastic lens materials
- Cloth backing helps the pad to conform to the tool and is easy to remove
- 250 pads per roll

Specifications:

Part #	Description
EL2-WHITE	7-petal, 3" tabbed, for base pads
EL2-WHITE-16	16-petal, 3" round, for base pads
WHITE-7CSF	7-petal, 3" round, for bare tools
WHITE-7	7-petal 3" round, 2nd fine

Recommended for polishing:

Yellow Ultimate (349) Polish Pad
Free-Form AR Lens Polish

Recommended Usage:

Material	Fining		Polishing	
	Bar Pressure	Time	Bar Pressure	Time
Polycarbonate	.20-.25	2.5 min	.3-.35	6
Trivex	.20-.25	2.5 min	.3-.35	6
CR-39	.20-.25	1 min	.3-.35	6
High Index	.20-.25	1 min	.3-.35	6
Mid Index	.20-.25	50 sec	.3-.35	6
2nd Fine/Poly	.25 -.3	2 mins.		

For More Information Call 800-237-8154 or visit www.LookToPSI.com



PRACTICAL SYSTEMS INC.
11617 Prospect Drive • Odessa, FL 33556
(800) 237-8154 • Fax (800) 330-3800
www.LookToPSI.com